

AIRPURION mobile DUAL

...stands out for its extraordinary high disinfection performance, compact construction and low energy consumption. It is manufactured in accordance with currently valid laws, standards and rules.



Illustration: AIRPURION mobile DUAL

The AIRPURION mobile DUAL consists of two PURION UV lamps which are placed in a quartz-made immersion tube system. The UV lamps are assembled on a robust and mobile rack. The controlling is integrated in a switchbox made from stainless steel.

The AIRPURION mobile can be switched on and off via remote control. The UV radiators are equipped with a special Teflon coating to avoid the release of mercury or splinters in case of breakage of the UV lamps.

To monitor the service life of the UV lamps the AIRPURION mobile is equipped with an Operating Time Counter (OTC).

The PURION UV-lamps are characterized by a long durability and a high degree of efficiency respecting to disinfection and energy consumption.

The compact construction allows for an easy removal of lamps or lamp exchange at the end of the lamps service life. It is not necessary to use additional tools.

The AIRPURION mobile DUAL is perfectly suitable for disinfection purposes in existing clean room environments. For operation it is not necessary to take structural measurements which could harm certificates etc.

manufacturer	PURION® GmbH
type	AIRPURION mobile DUAL
disinfection performance	suitable up to a room volume of approx. 200 m³
dimensions L x B x H in mm	500 x 470 x 1550
weight	23 kg
life time of PURION UV lamps	10.000 h
number of PURION UV lamps	2
protection grade	IP 65
electrical connection	110-240 V 50/60 Hz
total power	2 x 90 W
over current protection	10 A

details about disinfection performance:

guaranteed UVC dose ¹	distance from PURION UV lamp	
	2 m	5 m
200 J/m²	15 minutes	70 minutes
600 J/m²	50 minutes	200 minutes
1000 J/m²	80 minutes	340 minutes

This UV plant is applied at:

Clean room industry	•
Medicine and laboratories environment	•
Ripening rooms	•

Advantages

- chemical free
- high HACCP compliance due to splinter protection, monitoring system and remote control
- easy maintenance and low operational costs

¹ A dose of 200 J/m² ensures a 99% disinfection in case of mild contamination e.g. with Influenza; a dose of 600 J/m² ensures a 99% disinfection in case of moderate contamination e.g. with Baccillus tuberculi; a dose of 1000 J/m² ensures a 99% disinfection in case of severe contamination e.g. with Polio- and Echoviruses.